

Vault™ Self Cleaning HYPO Specifications

MIOX Corporation's new VAULT™ small series on-site generator is the first of its kind. Designed for high efficiency, low lifecycle cost, durability and reliability, the self-cleaning VAULT with self-adjusting flow control is virtually maintenance free. With over 40% improved salt and energy efficiencies and a new self-cleaning system, the VAULT is built for cost-effective, problem-free operation. The VAULT features an easy-to-upgrade cell to convert between sodium hypochlorite and advanced mixed oxidant with expandable capacity for the ultimate flexibility. Using just salt and power to generate a dilute chlorine-based solution eliminates the storage and handling of hazardous disinfection chemicals while providing a chlorine residual.

	H Vault 25	H Vault 50	H Vault 75	H Vault 100
Rated FAC Capacity	25 lbs/day 11.3 kg/day	50 lbs/day 22.7 kg/day	75 lbs/day 34 kg/day	100 lbs/day 45.4 kg/day
Water Treatment Capacity (at 1 ppm FAC)	3.0 MGD 11,355 m³/day	6.0 MGD 22,710 m³/day	9.0 MGD 34,065 m³/day	12.0 MGD 45,420 m³/day
Salt Conversion (SCE)*	3.0 lb salt/lb FAC 3.0 kg salt/kg FAC			
Energy Conversion (ECE) *	2.0 kW-hr/lb FAC 4.4 kW-hr/kg FAC			
FAC Concentration*	6,500 mg/L (+/- 1,000)			
Flow Rate	22.5 gph (+/- 15%) 85.2 lph (+/- 15%)	45 gph (+/- 15%) 170.4 lph (+/- 15%)	67.5 gph (+/- 15%) 255.6 lph (+/- 15%)	90 gph (+/- 15%) 340.8 lph (+/-15%)
Electrical Service Requirement	220 VAC, 1 ph, 30A, 50/60 hertz	220 VAC, 1 ph, 60A, 50/60 hertz	220 VAC, 1 ph, 90A, 50/60 hertz	220 VAC, 1 ph, 120A, 50/60 hertz
Number of Dedicated Circuits	1			
Air Temp. Required	45° to 110° F 7.2° to 43.3° C			
Feed Water Temp. Required	50° to 80° F 10° to 26.7° C			
Feed Water Pressure	>25 <100 psi >172 <689 kPa			
Energy Add for Internal Vent (kW)	0.7	1.4	2.1	2.8
Dimensions (WxDxH)	38 x 18 x 64.25 inches 96.5 x 45.7 x 163.2 cm			
Shipping Size (WxDxH)	TBD			
Shipping Weight (appx.)	TBD			
Self Cleaning	YES			


^{*} Performance may vary depending on salt quality, water quality, and temperature.

Note: This electronic document is controlled. Once this document is printed it becomes uncontrolled and obsolete. Refer only to electronic document for the latest information.









Vault™ Self Cleaning HYPO Drawing

Note: This electronic document is controlled. Once this document is printed it becomes uncontrolled and obsolete. Refer only to electronic document for the latest information.